



## TECHNICAL BULLETIN

### PDR1520NNF

**PRODUCT:** Quick Release 15 micron Dura Film

**PRIMARY USE:**

- Precision one step fining pad for CR39 and Hi Index lenses during ophthalmic manufacturing.
- Precision 2<sup>nd</sup> Fine fining pad for polycarbonate lenses during ophthalmic manufacturing.

**DESCRIPTION:**

3" 7 leaf 3M 15 micron Dura Film abrasive with Quick Release compensated backing designed for use with plastic or abrasive base pads. Back side of abrasive is laminated with HiBond, short term repositionable pressure sensitive adhesive for firm, temporary positioning onto base pads.

**LINER:**

Bleached, densified kraft paper.

**RECOMMENDED TIMES AND PRESSURE:**

**CR39/Hi Index**

LOH	45-90 seconds @ .3 to .4 bar
Coburn / Optek	45-90 seconds @ 16-18 psi

**Polycarbonate**

LOH	1 – 1 ½ minutes @ .3 to .4 bar
Coburn / Optek	1 – 1 ½ minutes @ 16-18 psi

**TYPICAL PHYSICAL PROPERTIES:**

- Thickness:
 

Pad Material & Adhesive.....	.016 " / .41mm (+/-0.001")
Liner.....	4.8 mils (+/-0.2 mils)
- Peel Adhesion:
 

PSTC-101	
Lined side... 180 degrees @ 12 IPM, 20 min. dwell.	
- Dynamic Shear:
 

PSTC-7	
Lined side...2500 grams (5.5 lb.) load on stainless	

**PACKAGING:**

Labeled in core with lot number information with plastic protective wrapping.

*No warranties are made in this Bulletin. All information, recommendations and descriptive material concerning DAC products are based upon research which is believed to be reliable but shall not constitute a warranty. Accordingly, all DAC products are sold with the understanding that purchaser will be solely responsible for determining the suitability of the materials for any purpose.*